

ergotron®

moving you forward

Zido® EMR Cart Package

- Find a comfortable height whether sitting or standing
- Squeeze the lever and a pneumatic cylinder moves the surface to any height between 30" and 44" (76–102 cm)
- Zido's heavy cast-metal base provides a very stable foundation
- Even though it's small to fit tight spaces, this cart holds up to 146 lbs (66.4 kg) overall *
- Different Zido accessories install on the front or the back of the column to maximize your space
- Add storage, cable management, or keyboard and monitor mounts
- The column has holes in 1" (2.5 cm) increments to install shelves, bins and other accessories at exactly the right height
- With a footprint of just 22" by 22" (56 x 56 cm), this cart fits easily in tight spaces, so it can go everywhere you do
- The 17"-wide (43 cm) handle makes it easy to steer anywhere you need go



HEIGHT-ADJUSTABLE EMR CART—CARRY YOUR LAPTOP OR TABLET ON A COMPACT, EASY-TO-STEER CART THAT TAKES EVERYTHING YOU NEED RIGHT TO YOUR PATIENT

This stripped-down, height-adjustable cart is perfect for transporting a laptop or tablet directly to a patient. The cart's tiny footprint makes it easy to fit in tiny spaces, and its wide handle makes it easy to move around. Add additional accessories for more customization.

Zido® EMR Cart Package

- 1 **Handle** The 17" (43.18 cm) wide handle makes the cart easy to steer
- 2 **Adjustable Height** Set the worksurface height 30"–40" (76.2–101.6 cm) so it's comfortable for patients and clinicians
- 3 **Cast Metal Base** The stability you need when steering through busy hallways
- 4 **Contoured Top** A 0.25" (0.64 cm) high lip runs all the way around the 0.75" (1.9 cm) thick cap worksurface to keep your laptop or tablets in place
- 5 **Compact Footprint** At just 22" (55.88 cm) wide, 22" (55.88 cm) deep, the cart fits into tight spaces
- 6 **Large Casters** The 4" (10.16 cm) diameter twin-wheel casters (2 locking) travel easily over thresholds and directly to the point of care



Part # (color)	BZD01CG/CG4 (cool grey)
Materials and Finishes	The steel column and cast metal base receive a baked-on powder coated finish that's durable and easy to clean. Worksurface is medium density fiberboard wrapped in Comfort Edge thermoplastic laminate that resists cracking and chipping and stands up to a wide range of chemicals
Column Height Range	30" (76.2 cm) to 40" (101.6 cm)
Optimal Load *	16-30 lbs. (7.26-13.61 kg)
Weight Capacity *	40 lbs. (18.2 kg) on the worksurface; 146 lbs. (66.4 kg) overall
Base Dimensions	17"W x 22.25"D (43.18 x 56.52 cm)
Worksurface Dimensions	22" x 17" (56 x 43 cm)
Mobility	Easy to move with 4" (10.16 cm) twinwheel rubber casters (two locking). Heavy cast metal base provides stability
Product Weight	44 lbs. (20 kg)
Shipping Weight	56 lbs (25.5 kg); Ships in 2 boxes
Warranty	Limited lifetime; five (5) years for pneumatic cylinder

* When calculating the load being applied to the cart's column and worksurface, also factor the weight of any accessory options that are being installed. The listed capacity for the Zido EMR Cart Package factors the additional weight of the handle (4 lbs/1.8 kg). Without addition of packaged accessories, the Zido Cart's total weight capacity = 150 lbs (68.2 kg)

Download additional resources at ergotron.com.

For more information:

Americas: 800.888.8458 / +1.651.681.7600 / insidesales@ergotron.com

EMEA: +31.33.45.45.600 / info.eu@ergotron.com

APAC: apaccustomerservice@ergotron.com

Custom: custom@ergotron.com

© Ergotron, Inc. 08.06.2020

Literature made in the U.S.A. Content subject to change.

Ergotron devices are not intended to cure, treat, mitigate or prevent any disease.

Patent information available at www.ergotron.com/patents.

WorkFit, StyleView, LearnFit, Neo-Flex, PowerShuttle, LiFeKinex, CareFit and eKinex are trademarks of Ergotron.

