



## Mesh Backs

Choose between two back heights.

Mid & High-Back Sizes AF5X4 AF5X8 Mid-Back version **High Back version** — 19.75"w —→ 24"h 20.5"h Ex. Model# AF564 Ex. Model# AF568

Headrest

AF5X9

High Back w/ Mesh Headrest (default)



Ex. Model# AF569



# Mesh Backs (Other Models)

### Stools

#### **Grande Spider Base (GSP)**

- -Spider base w/ chrome flat fixed footring
- -Stool package w/ 8" chrome cylinder
- -22" fixed footring
- -65mm soft casters



22" Fixed Footring

### **Adjustable Footring**

- -Knobless, turn-lock footring
- -Stool package w/ 10" chrome cylinder
- -20" adjustable footring
- -55mm black carpet casters




20" Adjustable Footring

## Nest



Armless option available





or

Black powdercoated steel tube with perpendicular leg endings for ideal mobility.

### Guest



Cantilever base with black, powdercoated finish rear button glides (removable to allow rearward sliding), & black polypropylene front stops for added stability.



## Mesh Colors

Choose between 2 standard soft touch colors.



# Knit (overlay option)

A permanent, warm & breathable knit overlay with 9 lively color choices.







Echo Park



Sawtelle



Silver Lake



Topanga



Palisades



Malibu



Joshua Tree



Sunset Junction



# Mesh Backs (Selected Accessories)

### Coat Rack



Black powdercoated wire rod coat hanger w/ collar support

### Deluxe Headrest



3-way adjustable slidable & upholstered Grade 3 leather-like material

### 2-way Headrest



Upholstered 2-way Headrest Grade 3 leather-like material

### Model-LX



Mesh Back Overlay (-LX)



Ex. Model# AF508-LX

Dress up your Affirm with a luxury French-stitched mesh back overlay.












## Cushioned Backs

Choose between multiple styles.



Ex. Model# AF418





# Seat Options

Affirm's generous waterfall curve combined with mild contours, allows "sit-as-you-like" comfort.

Combine the optional petite seat with the petite base package for even smaller dimensions.

### Standard

20.75" W

**Large Affirm seat**Std on Mesh High Back models:
AF516S, AF5x8, and AF5x9

19" W

Small Affirm seat
Std on Mesh Mid-Back and
Cushioned Back models: AF511S,
AF513, AF515, AF4xy, and
AF5X4 models



Ex. Model# AF528-5302



Fx. Model# AF488

### Optional

### 18" W

### Petite Truly. seat

- Seat shape will be different from Affirm std. seat
- Upcharge will apply



Ex. Model# AF514-5308



# Finish Options

Choose between a timeless black finish, or polished for high-end aesthetics.

For a lower seat height choose a petite package.

### **Polished Aluminum Package**



#### Includes:

- •27" Polished Aluminum Base
- 5" Chrome Cylinder

### **Black Finish Package**



#### Includes:

- •27" Black Nylon Base
- 5" Black Powdercoat Cylinder

### **Petite Silver Base Package**



#### Includes:

- Silver, 28" Engineered Nylon Base
- ~4" Black Powdercoat Petite Cylinder
- Black, 55mm dual-surface casters

### **Petite Black Base Package**



#### Includes:


- Black, 27" Engineered Nylon Base
- ~4" Black Powdercoat Petite Cylinder
- Black, 55mm dual-surface casters



## Mechanism Adjustments

#### **Executive Synchro** (Model AF428, AF524, AF528, AF529)

- A. Seat Height
- B. Seat Slider
- C. 5 position Tilt Lock\*
- D. Tilt Tension (telescopes out/in)
- E. Independent Back Angle




- A. Seat Height
- B. Seat Slider
- C. 3 position Tilt Lock\*
- D. Tilt Tension



- A. Seat Height
- B. Seat Slider
- C. 1 position Tilt Lock (push in)
- D Tilt Tension



- A. Seat Height
- B. Seat Slider
- C. 3 position Tilt Lock\*



#### **Full Multi-Function** (Model AF4**8**8, AF5**8**4, AF5**8**8, AF5**8**9)

- A. Seat Height
- B. Seat Slider
- C. Seat/Back Tilt and Lock
- D. Independent Back Angle
- E. Tilt Tension

INDEPENDENT MOTION

SIMPLE MOTION

F. Forward Seat Angle (for perching & back relief)



- A. Seat Height
- B. Seat Slider
- C. Seat/Back Tilt and Lock
- D. Independent Back Angle
- Stools (Model AF413, AF415, AF513, AF515)
- A. Seat Height
- B. Seat Slider
- C. Independent Back Angle



#### \*Positive Back Release

After unlocking the Tilt Lock lever, lean into the backrest to release the tilt lock & resume normal tilt recline motion.

SYNCHRONIZED MOTION