

Verify that you have all the hardware needed for the assembly.

Phillips-head screwdriver



5/16" or 8mm Hex
Drive Socket



#12 x 1/2" Tap Hex
Sheet Metal Screw



#12 x 3/4" Pan Head
Sheet Metal Screw





M4 Hex Wrench



Spacer (2)



#M6x12mm Button Cap Screws (included with table assembly)



#12x1/2" Tap Hex Sheet Metal Screws



WE IMPROVE YOUR LIFE

DESIGNED IN DENMARK

Type : DL5000XN0445590

Item No. : DL5N0013

Prod Date : 2011.10.11 506133971

Max Load : Push 800 N

Power Rate : 18 V ~ / Max. 10.0 Amp

Duty Cycle : 10 % Max. 2 min / 18 min

NOT TO BE OPENED BY UNAUTHORIZED PERSONNEL

P.O. 1506354-0128 MADE BY LINAK A/S DENMARK

←-----Attach the spacer to the leg motor with the #M6 x 12mm Button Cap Screws-----→



<--Attach the support angle to the spacer with the #12x1/2" Tap Hex Sheet Metal Screws-->

WE IMPROVE YOUR LIFE
DESIGNED IN DENMARK
Type : DLS000XN044
Item No. : DLSN0013
Prod Date : 2011.10.11 S.C
Max Load : Push 800 N
Power Rate: 18V=1 Max
Duty Cycle : 10 % Max 2 m
NOT TO BE OPENED BY UNAK
P.O.1506354-0128 MADE

Secure the spacer to the table top with the #12x3/4" Pan Head Hex Sheet Metal Screws



Secure the support angle to the table top with the #12x3/4" Pan Head Hex Sheet Metal Screws